

IDIV

IFIL STUCCO

Appearance	white thick paste
Constitution	resins with inorganic binders
pH	8-9
Character	anionic
Active substance	50%

Method of use

IFIL STUCCO is a speciality studied to recover and upgrade leather with many defects. Thanks to its formulation the defects are perfectly masked and the leather fully recovered.

IFIL STUCCO can be applied by hand using appropriate tool or by roll coating machine. In both cases the leather must rest overnight before embossing in order to allow the product to adhere to the leather at best.

When applied by roll coating machine the viscosity should be reduced to a suitable value diluting **IFIL STUCCO** with water and adding a casein binder like **BI 11**.

IFIL STUCCO is offered in three formulations:

IFIL STUCCO R medium viscosity for roll coating machine;
IFIL STUCCO S high viscosity for hand application;
IFIL STUCCO SK very high viscosity for hand application.

edition 07/2001

The information given herein is, to the best of our knowledge true and accurate. But it is given as a guidance only and is not to be taken as a warranty of results.